



FIST® Fiber Splice Tray with Field Installable DWDM, 4 Channels and upgrade port, Double Demultiplexing, 1551.72nm starting wavelength, 100GHz channel spacing, all fibers at right side

Product Classification

Regional Availability	EMEA
Product Type	DWDM splice tray
Product Brand	FIST®
Product Series	FIST-FDASA2

General Specifications

Application	For use with FIST fiber splice closures For use with FIST panels
Interface, Input	Stub tail
Interface, Output	Stub tail

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

