

CZ1840-000 | OCC1P-23200-S2SESEB

OCC1P Wideband Splitter, planar, singlemode, 2x32, symmetrical split ratio, SC/APC, 0.9 mm cable, medium duty housing



Product Classification

Regional Availability	EMEA Latin America North America
Product Type	Splitter component
Product Series	OCC1P

General Specifications

Device Type	Component, rectangular
Functionality	Splitting
Technology Type	Planar lightwave circuit (PLC)
Application	For use in FOSS closures
Circuits, quantity	1
Distribution Type	2 x 32 splitter
Interface, Input	SC/APC
Interface, Output	SC/APC
Split Ratio	Symmetrical
Splitter, quantity	1

Dimensions

Pigtail Length, Input	1.5 m 4.921 ft
Pigtail Length, Output	1.5 m 4.921 ft
Pigtail Diameter, Input	0.9 mm 0.035 in
Pigtail Diameter, Output	0.9 mm 0.035 in

Environmental Specifications

CZ1840-000 | OCC1P-23200-S2SESEB

Qualification Standards

Telcordia GR-1209-CORE | Telcordia GR-1221-CORE

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted

UK-ROHS Compliant/Exempted

