EF5492-000 | OCC1A-1210-NNANQNF

OCC1A Wideband Splitter, singlemode, 1x2, 90/10 ratio, 0.250 mm cable, field installable



Product Classification

Regional Availability North America

Product Type Splitter component

Product Series OCC1A

General Specifications

Device Type Component, tubular

Functionality Splitting

Technology Type Fused biconic tapered

Application For use in FOSC closures

Circuits, quantity 1

Distribution Type 1 x 2 splitter

Interface, InputStub tailInterface, OutputStub tailSplit Ratio90/10

Splitter, quantity 1

Dimensions

Pigtail Length, Input
2.5 m | 8.202 ft

Pigtail Length, Output
2.5 m | 8.202 ft

Pigtail Diameter, Input
0.25 mm | 0.01 in

Pigtail Diameter, Output
0.25 mm | 0.01 in

Packaging and Weights



EF5492-000 | OCC1A-1210-NNANQNF

Packaging quantity

1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

