

1316MCLICK



Miniature Click-on Hanger for 13–16 mm cable - Hardware Sold Separately

Product Classification

Product Type	Hanger kit
Product Brand	HELIAX®
Ordering Note	CommScope® non-standard product

General Specifications

Cables per Hanger	2
Color	Black
Hanger Type	Click-on hanger
Mounting	M8 through hole

Dimensions

Maximum Stack Height	3
Height	38.1 mm 1.5 in
Width	24.9 mm 0.98 in
Length	55.1 mm 2.169 in
Compatible Cable Diameter Range	13–16 mm
Compatible Diameter, maximum	16.3 mm 0.642 in
Compatible Diameter, minimum	13.7 mm 0.539 in
Nominal Size	1/2 in 3/8 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Engineered plastic
----------------------	--------------------

1316MCLICK

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Environmental Strength Capability Double cable weight

UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed 44.7 cm | 17.598 in

Width, packed 39.4 cm | 15.512 in

Length, packed 17.7 cm | 6.969 in

Packaging quantity 10

Weight, gross 0.05 kg | 0.11 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power