

760248943



Kit, SMB, 1 Fiber Port, 1 Power Port, White

Powered Fiber Cable Surface Mount Box Kit, 1 Fiber Port, 1 Power Port, White

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Surface mount module
Product Series	SL Series SLX Series

General Specifications

Application	Powered fiber
Color	Alpine white
Interface Feature, front	Fiber LC Duplex (1) Open SL Ports (2) Two wire terminals (1)
Mounting	Surface
Outlet Orientation	Flat
Port Marking Type	Label
Total Ports, quantity	4

Dimensions

Height	38 mm 1.496 in
Width	142.3 mm 5.602 in
Depth	116.2 mm 4.575 in

Electrical Specifications

Input Power	100 W (NEC Class 2)
Input Voltage	30 Vac 60 Vdc
Electrical Safety Standard	CB IEC 60950-1 IEC 62368-1 UL cUL

Material Specifications

Material Type	Polycarbonate
----------------------	---------------

Environmental Specifications

760248943

Environmental Space	Indoor
Flammability Rating	UL 94 V-0
Qualification Standards	NEC Class 2

Packaging and Weights

Packaging quantity	1
Weight, net	0.141 kg 0.31 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

