

# 19256B

---



Lace-up Hoisting Grip for HELIAX® 1.00-1.24 in (25.4-31.5 mm) cables, elliptical waveguide 77

## Product Classification

<b>Product Type</b>	Hoisting grip
<b>Product Brand</b>	HELIAX®
<b>Ordering Note</b>	CommScope® standard product (Global)

## General Specifications

<b>Attachment Spacing Intervals</b>	60.96 m   200 ft
<b>Hoisting Grip Type</b>	Lace-up hoisting grip
<b>Support Clamp</b>	Not included
<b>Tool Type</b>	Hoisting grip

## Dimensions

<b>Grip Length, minimum</b>	431.8 mm   17 in
<b>Leader Length, minimum</b>	330.2 mm   13 in
<b>Compatible Diameter, maximum</b>	31.5 mm   1.24 in
<b>Compatible Diameter, minimum</b>	25.4 mm   1 in
<b>Nominal Size</b>	7/8 in

## Electrical Specifications

<b>Return Loss Effect, maximum</b>	0.1 dB
<b>DTF Effect, maximum</b>	0.1 dB

## Material Specifications

<b>Material Type</b>	Stainless steel
----------------------	-----------------

## Mechanical Specifications

<b>Pull Load Capacity</b>	226.796 kg   500 lb
---------------------------	---------------------

# 19256B

---

## Packaging and Weights

<b>Height, packed</b>	38.1 mm   1.5 in
<b>Width, packed</b>	218.44 mm   8.6 in
<b>Length, packed</b>	220.98 mm   8.7 in
<b>Packaging quantity</b>	1
<b>Weight, gross</b>	0.22 kg   0.485 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

