

209800-47B1



Self-locking Hanger with Non transverse tab for 1-5/8 in RADIAX® Radiating cable

Product Classification

Product Type Hanger kit

General Specifications

Cables per Hanger 1

Color Black

Hanger Type Self locking hanger

Dimensions

Maximum Stack Height 2

Height 72.9 mm | 2.87 in

Width 22.1 mm | 0.87 in

Length 53.6 mm | 2.11 in

Compatible Diameter, maximum 50.5 mm | 1.988 in

Compatible Diameter, minimum 46.5 mm | 1.831 in

Nominal Size 1-5/8 in

Material Specifications

Material Type Polyamide PA12

Mechanical Specifications

Maximum Load 1400 N | 314.733 lbf

Environmental Specifications

Operating Temperature -40 °C to +80 °C (-40 °F to +176 °F)

209800-47B1

Flammability Test Method	UL 94-HB
Toxicity Index Test Method	IEC 60754-2
UV Resistance, minimum with no degradation	≥500 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed	11.5 cm 4.528 in
Width, packed	8.5 cm 3.346 in
Length, packed	30 cm 11.811 in
Packaging quantity	25
Weight, gross	2.1 kg 4.63 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power