

# 209800-47B



Self-locking Hanger for 1-5/8 in RADIAX® Radiating cable

## Product Classification

**Product Type** Hanger kit

## General Specifications

**Cables per Hanger** 1

**Color** Black

**Hanger Type** Self locking hanger

## Dimensions

**Maximum Stack Height** 2

**Height** 72.9 mm | 2.87 in

**Width** 22.1 mm | 0.87 in

**Length** 53.6 mm | 2.11 in

**Compatible Diameter, maximum** 50.5 mm | 1.988 in

**Compatible Diameter, minimum** 46.5 mm | 1.831 in

**Nominal Size** 1-5/8 in

## Material Specifications

**Material Type** Polyamide PA12

## Mechanical Specifications

**Maximum Load** 1400 N | 314.733 lbf

## Environmental Specifications

**Operating Temperature** -40 °C to +80 °C (-40 °F to +176 °F)

**Flammability Test Method** UL 94-HB

**Toxicity Index Test Method** IEC 60754-2

**UV Resistance, minimum with no degradation** ≥500 hours exposure in accelerated UV life chamber

# 209800-47B

---

## Packaging and Weights

Height, packed	11.5 cm   4.528 in
Width, packed	8.5 cm   3.346 in
Length, packed	30 cm   11.811 in
Packaging quantity	25
Weight, gross	2.1 kg   4.63 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power