

243095-1



Stainless Steel Hardware Kit for 1/2 in or 7/8 in Block style hangers, includes 3/8 in bolts and hardware, 177.8 mm (7 in) length

Product Classification

Product Type	Hardware kit
Ordering Note	CommScope® standard product (Global)

General Specifications

Thread Size	3/8 in
--------------------	--------

Dimensions

Maximum Stack Height	3
Length	177.8 mm 7 in
Nominal Size	1/2 in 7/8 in

Material Specifications

Material Type	Stainless steel 304
----------------------	---------------------

Packaging and Weights

Height, packed	254 mm 10 in
Width, packed	88.9 mm 3.5 in
Length, packed	88.9 mm 3.5 in
Included	Forty flat washers Forty lock washers Ten 3/8 in threaded rods Twenty hex nuts
Packaging quantity	10
Weight, gross	1.361 kg 3 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

* Footnotes

243095-1

Maximum Stack Height Fiber, Hybrid, Power