

# 243095-8

---



Stainless Steel Hardware Kit for 1-1/4 in or 1-5/8 in Block style hangers, includes M10 bolts and hardware, 185.92 mm (7.32 in) length

## Product Classification

<b>Product Type</b>	Hardware kit
<b>Product Brand</b>	HELIAX®
<b>Ordering Note</b>	CommScope® non-standard product

## General Specifications

**Thread Size** M10

## Dimensions

<b>Maximum Stack Height</b>	2
<b>Length</b>	185.928 mm   7.32 in
<b>Nominal Size</b>	1-1/4 in   1-5/8 in

## Material Specifications

**Material Type** Stainless steel 304

## Packaging and Weights

<b>Height, packed</b>	190.5 mm   7.5 in
<b>Width, packed</b>	114.3 mm   4.5 in
<b>Length, packed</b>	83.82 mm   3.3 in
<b>Included</b>	Forty flat washers   Forty lock washers   Ten M10 threaded rods   Twenty hex nuts
<b>Packaging quantity</b>	10
<b>Weight, gross</b>	1.51 kg   3.33 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power