

243095-9



Stainless Steel Hardware Kit for 1/2 in or 7/8 in Block style hangers, includes 3/8 in bolts and hardware, 95.25 mm (3.75 in) length

Product Classification

| | |
|----------------------|---------------------------------|
| Product Type | Hardware kit |
| Product Brand | HELIAX® |
| Ordering Note | CommScope® non-standard product |

General Specifications

Thread Size 3/8 in

Dimensions

| | |
|-----------------------------|--------------------|
| Maximum Stack Height | 1 |
| Length | 95.25 mm 3.75 in |
| Nominal Size | 1/2 in 7/8 in |

Material Specifications

Material Type Stainless steel 304

Packaging and Weights

| | |
|---------------------------|--|
| Height, packed | 149.86 mm 5.9 in |
| Width, packed | 63.5 mm 2.5 in |
| Length, packed | 63.5 mm 2.5 in |
| Included | Forty flat washers Forty lock washers Ten 3/8 in threaded rods Twenty hex nuts |
| Packaging quantity | 10 |
| Weight, gross | 1.052 kg 2.32 lb |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power