



Flex-Twist Hanger Assembly for WR112

Product Classification

Product Type Hanger kit

General Specifications

Cable Type Elliptical waveguide

Cables per Hanger 1

Color Silver

Hanger Type Flex-Twist hanger

Mounting 4.5 in OD pipe

Dimensions

Height 56.9 mm | 2.24 in

Width 127 mm | 5 in

Length 800 mm | 31.496 in

Waveguide Size WR112 | WG15 | R84

Material Specifications

Material Type Stainless steel

Mechanical Specifications

Wind Speed, survival with 1/2 in (12 mm) radial ice 201.167 km/h | 125 mph

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Corrosion Test Method MIL-F-14072C | MIL-STD-889B

Packaging and Weights

Included Clamp | Rubber grommet | Threaded rod

244106A-84

Packaging quantity	1
Weight, gross	0.64 kg 1.411 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system