

245172



Cold shrink Kit for 1-5/8 in or 1-1/4 in to 1/4 in through 1/2 in connections

Product Classification

| | |
|----------------------|--------------------------------------|
| Product Type | Cold shrink kit |
| Product Brand | HELIAX® |
| Ordering Note | CommScope® standard product (Global) |

General Specifications

| | |
|-----------------------------|---|
| Application | Provides additional moisture seal for cable connections |
| Applications per Kit | One 1/4 in–1/2 in to 1-5/8 in or 1-1/4 in |
| Cable Family | AL7-50 AVA7-50 EFX2-50 ETS1-50T ETS2-50T FSJ1-50B FSJ1-75 FSJ2-50 FSJ4-50B FSJ4-75A LDF1-50 LDF2-50 LDF4-50A LDF4-75 LDF6-50 LDF7-50A VXL6-50 VXL7-50 |
| Color | Black |

Dimensions

| | |
|---|--|
| Width | 72.39 mm 2.85 in |
| Length | 330.2 mm 13 in |
| Cable Diameter for Seal, maximum | 30.48 mm 1.2 in |
| Cable Diameter for Seal, minimum | 7.37 mm 0.29 in |
| Inner Diameter | 69.85 mm 2.75 in |
| Nominal Size | 1-1/4 in 1-5/8 in 1/2 in 1/4 in 3/8 in |

Material Specifications

| | |
|----------------------|-------------|
| Material Type | EPDM rubber |
|----------------------|-------------|

Environmental Specifications

| | |
|---|--|
| UV Resistance Test Method | UV condensation reference ASTM-G-53, light source UVA 340 fluorescent lamp |
| UV Resistance, minimum with no degradation | ≥1000 hours |

Weather Resistance Test Method 04AS00-03.6.0 | IEC 60529:2001, IP67 | MIL-STD-1344A, Method 1002

Packaging and Weights

Height, packed 299.72 mm | 11.8 in
Width, packed 81.28 mm | 3.2 in
Length, packed 81.28 mm | 3.2 in
Included One EPDM rubber tube | One sealing foam strip
Packaging quantity 1
Weight, gross 0.34 kg | 0.75 lb

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |