



Single Entrance Panel for elliptical waveguide 77

Product Classification

**Product Type** Entrance panel

General Specifications

**Color** Gray

**Entry Panel Port Size** 101.6 mm | 4 in

**Number of Ports** 1

**Panel Type** Single

Dimensions

**Height** 76.2 mm | 3 in

**Width** 127 mm | 5 in

**Waveguide Size** WR112 | WG15 | R84

Material Specifications

**Material Type** Aluminum

Environmental Specifications

**Weather Resistance Test Method** 04AS00-03.9.0 | IEC 60529.14.2

Packaging and Weights

**Height, packed** 180.34 mm | 7.1 in

**Width, packed** 180.34 mm | 7.1 in

**Length, packed** 180.34 mm | 7.1 in

**Included** Boot | Plate

**Packaging quantity** 1

**Weight, gross** 0.91 kg | 2.006 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.andrew.com/ProductCompliance">www.andrew.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



Included Products

204673-1	- One 4" Port Entrance Panel 1 x 1
WGB4-77	- Boot Assembly, 4 in, for elliptical waveguide 77



One 4" Port Entrance Panel 1 x 1

Product Classification

Product Type	Entrance panel
Ordering Note	ANDREW® non-standard product

General Specifications

Color	Gray
Entry Panel Port Size	101.6 mm   4 in
Number of Ports	1
Panel Type	Single

Dimensions

Height	177.8 mm   7 in
Width	177.8 mm   7 in

Material Specifications

Material Type	Aluminum
---------------	----------

Environmental Specifications

Weather Resistance Test Method	04AS00-03.9.0   IEC 60529:2001, IP66
--------------------------------	--------------------------------------

Packaging and Weights

Height, packed	177.8 mm   7 in
Width, packed	177.8 mm   7 in
Length, packed	40.64 mm   1.6 in
Included	Entry cap   Hardware   Port
Packaging quantity	1
Weight, gross	0.28 kg   0.617 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.andrew.com/ProductCompliance">www.andrew.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



# WGB4-77



Boot Assembly, 4 in, for elliptical waveguide 77

## Product Classification

**Product Type** Boot assembly

## General Specifications

**Cable Type** Elliptical waveguide

**Cables per Cushion** 1

**Color** Black

## Dimensions

**Width** 101.6 mm | 4 in

**Length** 76.2 mm | 3 in

**Waveguide Size** WR112 | WG15 | R84

## Material Specifications

**Material Type** EPDM rubber

## Environmental Specifications

**UV Resistance Test Method** MIL-STD-810E, Procedure 11, Method 557

**Weather Resistance Test Method** 04AS00-03.9.52 | IEC 60529:2001, IP66

## Packaging and Weights

**Height, packed** 139.7 mm | 5.5 in

**Width, packed** 139.7 mm | 5.5 in

**Length, packed** 152.4 mm | 6 in

**Included** Boot | Cushion

**Packaging quantity** 1

**Weight, gross** 0.25 kg | 0.551 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.andrew.com/ProductCompliance">www.andrew.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

