



Messenger Stainless Steel Cable Tie for RCT RADIAX® Radiating cables

Product Classification

Product Type Cable tie

General Specifications

Cables per Hanger 1

Hanger Type Cable tie

Mounting Messenger wire

Dimensions

Height 5.1 mm | 0.201 in

Width 7.9 mm | 0.311 in

Length 362 mm | 14.252 in

Compatible Diameter, maximum 102 mm | 4.016 in

Nominal Size 1-1/4 in | 1-5/8 in | 1/2 in | 7/8 in

Material Specifications

Material Type Stainless steel

Mechanical Specifications

Pullout Force, maximum with no cable slippage 700 N | 157.366 lbf

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Flammability Test Method UL 2043

Packaging and Weights

Packaging quantity 1

Weight, gross 0.01 kg | 0.022 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

