

# 250062

---



## Messenger Wire Tie Wrap with spacer for RCT RADIAX® Radiating cable

- For added support, use with Andrew Stainless Steel Cable Ties (250058) at 5 meter intervals

### Product Classification

**Product Type** Wire tie

### General Specifications

**Cables per Hanger** 1  
**Color** Black  
**Hanger Type** Cable tie  
**Mounting** Messenger wire

### Dimensions

**Height** 25.4 mm | 1 in  
**Width** 12.7 mm | 0.5 in  
**Length** 405.9 mm | 15.98 in  
**Compatible Diameter, maximum** 114 mm | 4.488 in  
**Nominal Size** 1-1/4 in | 1-5/8 in | 1/2 in | 7/8 in

### Material Specifications

**Material Type** Engineered plastic

### Mechanical Specifications

**Pullout Force, maximum with no cable slippage** 445 N | 100.04 lbf

### Environmental Specifications

**Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F)  
**Flammability Test Method** UL 94-HB  
**UV Resistance, minimum with no degradation** ≥100 hours exposure in accelerated UV life chamber

### Packaging and Weights

# 250062

---

**Packaging quantity** 1  
**Weight, gross** 0.02 kg | 0.044 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

