


252027-10KT-P



Hardware Kit for Miniature Click-on Hanger, includes 5/16" bolts and hardware, 3.24" (82mm) length, kit of 10

Product Classification

| | |
|----------------------|---------------------------------|
| Product Type | Hardware kit |
| Product Brand | HELIAX® |
| Ordering Note | CommScope® non-standard product |

Dimensions

| | |
|-----------------------------|--------------------------|
| Maximum Stack Height | 1 |
| Length | 82.296 mm 3.24 in |
| Nominal Size | 1/2 in 1/4 in 3/8 in |

Material Specifications

| | |
|----------------------|---------------------|
| Material Type | Stainless steel 304 |
|----------------------|---------------------|

Packaging and Weights

| | |
|---------------------------|--|
| Height, packed | 287.02 mm 11.3 in |
| Width, packed | 254 mm 10 in |
| Length, packed | 152.4 mm 6 in |
| Included | Ten 5/16 in bolts Ten flat washers Ten hex nuts Ten lock washers |
| Packaging quantity | 10 |
| Weight, gross | 1.002 kg 2.21 lb |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power