

29961-C



Lace-up Hoisting Grip with cable tie for HELIAX® 1.50-1.74 in (38.1-44.2 mm) cables and elliptical waveguide 64

Product Classification

Product Type	Hoisting grip
Product Brand	HELIAX®
Ordering Note	CommScope® standard product (Global)

General Specifications

Attachment Spacing Intervals	60.96 m 200 ft
Hoisting Grip Type	Lace-up hoisting grip
Support Clamp	Not included
Tool Type	Hoisting grip

Dimensions

Grip Length, minimum	635 mm 25 in
Leader Length, minimum	203.2 mm 8 in
Compatible Diameter, maximum	44.2 mm 1.74 in
Compatible Diameter, minimum	38.1 mm 1.5 in
Nominal Size	1-1/4 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Stainless steel
----------------------	-----------------

Mechanical Specifications

Pull Load Capacity	408.233 kg 900 lb
---------------------------	---------------------

29961-C

Packaging and Weights

Height, packed	55.88 mm 2.2 in
Width, packed	236.22 mm 9.3 in
Length, packed	236.22 mm 9.3 in
Packaging quantity	1
Weight, gross	0.38 kg 0.838 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

