



Lace-up Hoisting Grip for HELIAX® 1.50-1.74 in (38.1-63.5 mm) cables and elliptical waveguide 37

## Product Classification

<b>Product Type</b>	Hoisting grip
<b>Product Brand</b>	HELIAX®
<b>Ordering Note</b>	CommScope® non-standard product

## General Specifications

<b>Attachment Spacing Intervals</b>	60.96 m   200 ft
<b>Hoisting Grip Type</b>	Lace-up hoisting grip
<b>Support Clamp</b>	Not included
<b>Tool Type</b>	Hoisting grip

## Dimensions

<b>Grip Length, minimum</b>	660.4 mm   26 in
<b>Leader Length, minimum</b>	355.6 mm   14 in
<b>Compatible Diameter, maximum</b>	63.5 mm   2.5 in
<b>Compatible Diameter, minimum</b>	50.8 mm   2 in
<b>Nominal Size</b>	2-1/4 in

## Electrical Specifications

<b>Return Loss Effect, maximum</b>	0.1 dB
<b>DTF Effect, maximum</b>	0.1 dB

## Material Specifications

<b>Material Type</b>	Stainless steel   Tin-coated bronze
----------------------	-------------------------------------

## Mechanical Specifications

<b>Pull Load Capacity</b>	526.167 kg   1160 lb
---------------------------	----------------------

## Packaging and Weights

<b>Height, packed</b>	388.62 mm   15.3 in
<b>Width, packed</b>	83.82 mm   3.3 in
<b>Length, packed</b>	388.62 mm   15.3 in
<b>Packaging quantity</b>	1
<b>Weight, gross</b>	0.77 kg   1.698 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

