

3CCGRIP



Support Hoisting Grip for 0.27-0.35 in (7.0-9.0 mm) cables and ATCB-B01 series RET cable

Product Classification

Product Type	Hoisting grip
Product Brand	HELIAX®
Ordering Note	CommScope® non-standard product

General Specifications

Attachment Spacing Intervals	60.96 m 200 ft
Hoisting Grip Type	Support hoisting grip
Tool Type	Hoisting grip

Dimensions

Grip Length, minimum	142.24 mm 5.6 in
Leader Length, minimum	76.2 mm 3 in
Compatible Diameter, maximum	9 mm 0.354 in
Compatible Diameter, minimum	7 mm 0.276 in
Nominal Size	1/4 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	PPE
----------------------	-----

Mechanical Specifications

Pull Load Capacity	45.359 kg 100 lb
---------------------------	--------------------

Packaging and Weights

3CCGRIP

Height, packed	25.4 mm 1 in
Width, packed	254 mm 10 in
Length, packed	203.2 mm 8 in
Packaging quantity	1
Weight, gross	0.04 kg 0.088 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant