

43094



Lace-up Hoisting Grip for HELIAX® 0.62-0.74 in (15.7-18.7 mm) cables and elliptical waveguide 180 and 220

Product Classification

Product Type	Hoisting grip
Product Brand	HELIAX®
Ordering Note	CommScope® standard product in the United States and Canada

General Specifications

Attachment Spacing Intervals	60.96 m 200 ft
Hoisting Grip Type	Lace-up hoisting grip
Support Clamp	Not included
Tool Type	Hoisting grip

Dimensions

Grip Length, minimum	254 mm 10 in
Leader Length, minimum	177.8 mm 7 in
Compatible Diameter, maximum	18.7 mm 0.736 in
Compatible Diameter, minimum	15.7 mm 0.618 in
Nominal Size	1/2 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Stainless steel
----------------------	-----------------

Mechanical Specifications

Pull Load Capacity	226.796 kg 500 lb
---------------------------	---------------------

43094

Packaging and Weights

Height, packed	43.18 mm 1.7 in
Width, packed	187.96 mm 7.4 in
Length, packed	246.38 mm 9.7 in
Packaging quantity	1
Weight, gross	0.2 kg 0.441 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

