

Lace-up Hoisting Grip for HELIAX® 0.62-0.74 in (15.7-18.7 mm) cables and elliptical waveguide 180 and 220

Product Classification

Product Type Hoisting grip
Product Brand HELIAX®

Ordering Note ANDREW® standard product in the United States and Canada

General Specifications

Attachment Spacing Intervals 60.96 m | 200 ft

Hoisting Grip Type Lace-up hoisting grip

Support ClampNot includedTool TypeHoisting grip

Dimensions

Grip Length, minimum254 mm | 10 inLeader Length, minimum177.8 mm | 7 inCompatible Diameter, maximum18.7 mm | 0.736 inCompatible Diameter, minimum15.7 mm | 0.618 in

Nominal Size 1/2 in

Electrical Specifications

Return Loss Effect, maximum 0.1 dB

DTF Effect, maximum 0.1 dB

Material Specifications

Material Type Stainless steel

Mechanical Specifications

Pull Load Capacity 226.796 kg | 500 lb



43094

Packaging and Weights

 Height, packed
 43.18 mm | 1.7 in

 Width, packed
 187.96 mm | 7.4 in

 Length, packed
 246.38 mm | 9.7 in

Packaging quantity

Weight, gross 0.2 kg | 0.441 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

