68MCLICK



Miniature Click-on Hanger for 6–8 mm cable - Hardware Sold Separately (search MCLICK-SERIES-HARDWARE for options available)

Product Classification

Product Type	Hanger kit
Product Brand	HELIAX®
Ordering Note	ANDREW® non-standard product
General Specifications	
Cables per Hanger	2
Color	Black
Hanger Type	Click-on hanger
Mounting	M8 through hole
Dimensions	
Maximum Stack Height	3
Height	38.1 mm 1.5 in
Width	16 mm 0.63 in
Length	35.1 mm 1.382 in
Compatible Cable Diameter Range	5.8-8.1 mm
Compatible Diameter, maximum	8.1 mm 0.319 in
Compatible Diameter, minimum	5.8 mm 0.228 in
Nominal Size	1/4 in
Electrical Specifications	
Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB
Material Specifications	
Material Type	Engineered plastic

Page 1 of 2



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 2, 2025


68MCLICK

Mechanical Specifications

Vibration Survival	≥4 hours at resonant frequency
Environmental Specifications	
Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Environmental Strength Capability	Double cable weight
UV Resistance, minimum with no degradation	≥100 hours exposure in accelerated UV life chamber
Packaging and Weights	
Height, packed	30.4 cm 11.969 in
Width, packed	27.9 cm 10.984 in
Length, packed	2.5 cm 0.984 in
Packaging quantity	10
Weight, gross	0.09 kg 0.198 lb
Doculatory Compliance /Costificatio	

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



ke

Maximum Stack Height Fiber, Hybrid, Power