

BC-35-14D



Pipe-to-Pipe Clamp, joins two 2-3/8 in to 5 in OD round members

Product Classification

Product Type Clamp set

General Specifications

Mounting Pipe-to-pipe

Taper Non-tapered | Tapered

Dimensions

Height 152.4 mm | 6 in

Width 203.2 mm | 8 in

Length 355.6 mm | 14 in

Mounting Diameter 2, maximum 127 mm | 5 in

Mounting Diameter 2, minimum 60.96 mm | 2.4 in

Mounting Diameter, maximum 127 mm | 5 in

Mounting Diameter, minimum 60.96 mm | 2.4 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Clamp halves | Threaded rod

Packaging quantity 2

Weight, net 23.1 kg | 50.927 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted

BC-35-14D

UK-ROHS

Compliant/Exempted

