

BC-40-16D



Pipe-to-Pipe Clamp, joins two 4 in to 9 in OD round members

Product Classification

Product Type Clamp set

General Specifications

Mounting Pipe-to-pipe

Taper Non-tapered | Tapered

Dimensions

Height 152.4 mm | 6 in

Width 304.8 mm | 12 in

Length 406.4 mm | 16 in

Mounting Diameter 2, maximum 228.6 mm | 9 in

Mounting Diameter 2, minimum 101.6 mm | 4 in

Mounting Diameter, maximum 228.6 mm | 9 in

Mounting Diameter, minimum 101.6 mm | 4 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Clamp halves | Threaded rod

Packaging quantity 2

Weight, net 31.5 kg | 69.446 lb