

# BHD-12S

---



Double Block Hanger for 1/2 in coaxial cable (FSJ4)

## Product Classification

<b>Product Type</b>	Hanger kit
<b>Product Brand</b>	HELIAX®
<b>Ordering Note</b>	CommScope® standard product (Global)

## General Specifications

<b>Cables per Hanger</b>	2
<b>Color</b>	Black
<b>Hanger Type</b>	Double block hanger
<b>Mounting</b>	Mounting hole clearance for 3/8, 16 UNC or M10 threaded rod

## Dimensions

<b>Maximum Stack Height</b>	4
<b>Height</b>	40.1 mm   1.579 in
<b>Width</b>	33 mm   1.299 in
<b>Length</b>	67.1 mm   2.642 in
<b>Compatible Cable Diameter Range</b>	13.5–15.5 mm
<b>Compatible Diameter, maximum</b>	15.5 mm   0.61 in
<b>Compatible Diameter, minimum</b>	13.5 mm   0.531 in
<b>Nominal Size</b>	1/2 in

## Electrical Specifications

<b>Return Loss Effect, maximum</b>	0.1 dB
<b>DTF Effect, maximum</b>	0.1 dB

## Material Specifications

# BHD-12S

---

**Material Type** Engineered plastic

## Environmental Specifications

**Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

**Environmental Strength Capability** Double cable weight

**UV Resistance, minimum with no degradation** ≥100 hours exposure in accelerated UV life chamber

## Packaging and Weights

**Height, packed** 3.8 cm | 1.496 in

**Width, packed** 17.8 cm | 7.008 in

**Length, packed** 25.4 cm | 10 in

**Packaging quantity** 10

**Weight, gross** 0.37 kg | 0.816 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power