

BHD-14



Double Block Hanger for 1/4 inch coaxial cable

Product Classification

Product Type	Hanger kit
Product Brand	HELIAX®
Ordering Note	CommScope® standard product (Global)

General Specifications

Cables per Hanger	2
Color	Black
Hanger Type	Double block hanger
Mounting	Mounting hole clearance for 3/8, 16 UNC or M10 threaded rod

Dimensions

Maximum Stack Height	4
Height	36.1 mm 1.421 in
Width	19.1 mm 0.752 in
Length	32 mm 1.26 in
Compatible Cable Diameter Range	7–9 mm
Compatible Diameter, maximum	9 mm 0.354 in
Compatible Diameter, minimum	7 mm 0.276 in
Nominal Size	1/4 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

BHD-14

Material Type Engineered plastic

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Environmental Strength Capability Double cable weight

UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed 3.8 cm | 1.496 in

Width, packed 10.2 cm | 4.016 in

Length, packed 14 cm | 5.512 in

Packaging quantity 10

Weight, gross 0.11 kg | 0.243 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power