

# BHD-158

---



Double Block Hanger for 1-5/8 in coaxial cable

## Product Classification

|                      |                                      |
|----------------------|--------------------------------------|
| <b>Product Type</b>  | Hanger kit                           |
| <b>Product Brand</b> | HELIAX®                              |
| <b>Ordering Note</b> | CommScope® standard product (Global) |

## General Specifications

|                          |                                   |
|--------------------------|-----------------------------------|
| <b>Cables per Hanger</b> | 2                                 |
| <b>Color</b>             | Black                             |
| <b>Hanger Type</b>       | Double block hanger               |
| <b>Mounting</b>          | 3/8 in (M10) drilled cable ladder |

## Dimensions

|  |                    |
|--|--------------------|
| <b>Maximum Stack Height</b>            | 4                  |
| <b>Height</b>                          | 48 mm   1.89 in    |
| <b>Width</b>                           | 71.1 mm   2.799 in |
| <b>Length</b>                          | 136.9 mm   5.39 in |
| <b>Compatible Cable Diameter Range</b> | 49–51.1 mm         |
| <b>Compatible Diameter, maximum</b>    | 51.1 mm   2.012 in |
| <b>Compatible Diameter, minimum</b>    | 49 mm   1.929 in   |
| <b>Nominal Size</b>                    | 1-5/8 in           |

## Electrical Specifications

|                                    |        |
|------------------------------------|--------|
| <b>Return Loss Effect, maximum</b> | 0.1 dB |
| <b>DTF Effect, maximum</b>         | 0.1 dB |

## Material Specifications

# BHD-158

---

**Material Type** Engineered plastic

## Environmental Specifications

**Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

**Environmental Strength Capability** Double cable weight

**UV Resistance, minimum with no degradation** ≥100 hours exposure in accelerated UV life chamber

## Packaging and Weights

**Height, packed** 5.1 cm | 2.008 in

**Width, packed** 25.4 cm | 10 in

**Length, packed** 30.5 cm | 12.008 in

**Packaging quantity** 10

**Weight, gross** 1.38 kg | 3.042 lb

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| CHINA-ROHS    | Below maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |



## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power