

BHD-4MM



Double Block Hanger for 5 - 7 mm fiber cables

Product Classification

Product Type	Hanger kit
Product Brand	HELIAX®
Ordering Note	CommScope® standard product (Global)

General Specifications

Cables per Hanger	2
Color	Black
Hanger Type	Double block hanger
Mounting	Mounting hole clearance for 3/8, 16 UNC or M10 threaded rod

Dimensions

Maximum Stack Height	4
Height	56.1 mm 2.209 in
Width	33 mm 1.299 in
Length	67.1 mm 2.642 in
Compatible Cable Diameter Range	5–7 mm
Compatible Diameter, maximum	7 mm 0.276 in
Compatible Diameter, minimum	5 mm 0.197 in
Nominal Size	4 mm

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

BHD-4MM

Material Type Engineered plastic

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Environmental Strength Capability Double cable weight

UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed 5.7 cm | 2.244 in

Width, packed 17.8 cm | 7.008 in

Length, packed 25.4 cm | 10 in

Packaging quantity 10

Weight, gross 0.6 kg | 1.323 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power