

Double Block Hanger for 7/8 in coaxial cable - Hardware Sold Separately (search 243095-SERIES-HARDWARE for options avaliable)

Product Classification

 Product Type
 Hanger kit

 Product Brand
 HELIAX®

Ordering Note ANDREW® standard product (Global)

General Specifications

Cables per Hanger 2
Color Black

Hanger Type Double block hanger

Mounting 3/8 in (M10) drilled cable ladder

Dimensions

Maximum Stack Height 4

 Height
 42.9 mm | 1.689 in

 Width
 40.1 mm | 1.579 in

 Length
 80 mm | 3.15 in

 Compatible Cable Diameter Range
 27.7–28.2 mm

Compatible Diameter, maximum 28.2 mm | 1.11 in

Compatible Diameter, minimum 27.7 mm | 1.091 in

Nominal Size 7/8 in

Electrical Specifications

 Return Loss Effect, maximum
 0.1 dB

 DTF Effect, maximum
 0.1 dB

Material Specifications



BHD-78

Material Type Engineered plastic

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$

Environmental Strength Capability Double cable weight

UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

 Height, packed
 5.1 cm | 2.008 in

 Width, packed
 17.8 cm | 7.008 in

 Length, packed
 22.9 cm | 9.016 in

Packaging quantity 10

Weight, gross 0.56 kg | 1.235 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power

