

# CB3016-000 | FIST-FSASA2-16-1A-R

---



FIST® Fiber Splice Tray with Field Installable Splitter, symmetrical ratio, 1x6, FBT component, grade A, all fibers at right side

## Product Classification

|                              |                      |
|------------------------------|----------------------|
| <b>Regional Availability</b> | EMEA                 |
| <b>Product Type</b>          | Splitter splice tray |
| <b>Product Brand</b>         | FIST®                |
| <b>Product Series</b>        | FIST-FSASA2          |

## General Specifications

|                          |   |
|--------------------------|---|
| <b>Application</b>       | For use with FIST fiber splice closures |
| <b>Interface, Input</b>  | Stub tail                               |
| <b>Interface, Output</b> | Stub tail                               |

## Packaging and Weights

|                           |   |
|---------------------------|---|
| <b>Packaging quantity</b> | 1 |
|---------------------------|---|

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>   |
|---------------|---|
| CHINA-ROHS    | Above maximum concentration value   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant/Exempted  |
| UK-ROHS       | Compliant/Exempted  |

