CC-215-6



Crossover Clamp, joins 2-1/2 in to 3-1/2 in OD pipe to 2-3/8 in to 5 in OD pipe

Product Classification	
Product Type	Clamp set
General Specifications	
Mounting	Crossover clamp
Tower Taper	Non-tapered
Dimensions	
Height	127 mm 5 in
Width	203.2 mm 8 in
Length	127 mm 5 in
Mounting Diameter 2, maximum	127 mm 5 in
Mounting Diameter 2, minimum	60.96 mm 2.4 in
Mounting Diameter, maximum	88.9 mm 3.5 in
Mounting Diameter, minimum	63.5 mm 2.5 in
Material Specifications	
Material Type	Hot dip galvanized steel

Packaging and Weights

Included	Clamp halves Threaded rod
Packaging quantity	1
Weight, net	4.1 kg 9.039 lb

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

Page 1 of 1



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025