

Round Chimney Mount, 7–8 ft OD

Allows for standard sector frame to be mounted to a chimney utilizing (2) "760258156-001" interface brackets per sector frame. Ordered separate.

Sector frames ordered separate.

Site engineer of record to determine capacity and structure suitability for installation.

Product Classification

Product Type Chimney mount

Ordering Note ANDREW® non-standard product

Warranty One year

General Specifications

Mounting Round Chimneys, 2.13–2.44 m (7–8 ft) OD

Dimensions

 Height
 609.6 mm | 24 in

 Width
 1524 mm | 60 in

 Length
 1524 mm | 60 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact your local ANDREW representative

Wind Rating Test Method TIA/EIA-222

Packaging and Weights



CM-R78

Included Brackets | Hardware

Packaging quantity 1

Weight, net 136.1 kg | 300.049 lb

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

* Footnotes

Warranty For more information, please consult our Product Warranty guidelines

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

