

CM-R78



Round Chimney Mount, 7–8 ft OD

Allows for standard sector frame to be mounted to a chimney utilizing (2) "760258156-001" interface brackets per sector frame. Ordered separate.

Sector frames ordered separate.

Site engineer of record to determine capacity and structure suitability for installation.

Product Classification

Portfolio	CommScope®
Product Type	Chimney mount
Ordering Note	CommScope® non-standard product
Warranty	One year

General Specifications

Mounting	Round Chimneys, 2.13–2.44 m (7–8 ft) OD
-----------------	---

Dimensions

Height	609.6 mm 24 in
Width	1524 mm 60 in
Length	1524 mm 60 in

Material Specifications

Material Type	Hot dip galvanized steel
----------------------	--------------------------

Mechanical Specifications

Wind Rating	For Specifications, please contact steelproducts@commscope.com or call 800-255-1479
Wind Rating Test Method	TIA/EIA-222

CM-R78

Packaging and Weights

Included	Brackets Hardware
Packaging quantity	1
Weight, net	136.1 kg 300.049 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

* Footnotes

Warranty	For more information, please consult our Product Warranty guidelines
Wind Rating	BWS—Base Wind Speed; FBC—Florida Building Code