# CS-B-2



Cluster Support Bracket, u-bolt for 2-3/8 in OD round member attachment

#### **Product Classification**

Product Type Cluster Support Bracket

#### General Specifications

Cable Runs, quantity 7
Hole, quantity 7

**Mounting** Cluster support

#### Dimensions

 Height
 127 mm | 5 in


 Width
 228.6 mm | 9 in

 Length
 152.4 mm | 6 in

 Pipe Outer Diameter
 60.96 mm | 2.4 in

 Hole Size
 3/4 in | 7/16 in

# Outline Drawing



# Material Specifications

Material Type Hot dip galvanized steel

# Packaging and Weights

**Included** Brackets

Packaging quantity 1

**Weight, net** 1.8 kg | 3.968 lb

# Regulatory Compliance/Certifications

Agency Classification



Page 2 of 21

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

# Included Products

ACS-12	-	Antenna and RRU Cable Support Bracket for up to 12 Cables
CS-B	-	Cluster Support Bracket
GUB-4240	_	Galvanized U-bolt Assembly, 1/2 in x 2-1/2 in x 4 in
PG-CS08	_	PIM-Guard® Antenna and RRU Cable Support Bracket with 8 ports for stackable hangers (up to 3 per port). Install with torque wrench set at 10 to 15 ft-lb to meet carrier PIM requirements. For patents, see www.cs-pat.com
PG-CS23	_	PIM-Guard® Antenna and RRU Cable Support Bracket with 23 ports for stackable hangers (up to 3 per port). Install with torque wrench set at 10 to 15 ft-lb to meet carrier PIM requirements. For patents, see www.cs-pat.com
PG-CSEB17	_	PIM-Guard® Expansion Bracket - expands PG-CS08 Cable Support Bracket to 23 Ports. For patents, see www.cs-pat.com
PG-RM06	_	PIM-Guard® Round Member Cable Support Bracket 6 ports for stackable hangers (up to 3 per port). Install with torque wrench set at 5 to 7 ft-lb to meet carrier PIM requirements. For patents, see www.cs-pat.com
PG-RMBH12	_	PIM-Guard® Round Member Cable Support Bracket for Block Hangers - Two 3/8" threaded rods for up to 12 hangers. Install with torque wrench set at 10 to 15 ft-lb to meet carrier PIM requirements.
PG-RMBH12-BP	-	PIM-Guard® Round Member Cable Support Bracket for Block Hangers (pkg of 10)- Two 3/8" threaded rods for up to 12 hangers. Install with torque wrench set at 10 to 15 ft-lb to meet carrier PIM requirements.



#### Antenna and RRU Cable Support Bracket for up to 12 Cables

#### **Product Classification**

Product Type Antenna/RRU Cable Support

#### General Specifications

Cable Runs, quantity 12
Hole, quantity 12

**Mounting** Round member

#### **Dimensions**

 Width
 419.1 mm | 16.5 in

 Length
 294.64 mm | 11.6 in

 Mounting Diameter, maximum
 50.8 mm | 2 in

 Mounting Diameter, minimum
 254 mm | 10 in

 Hole Size
 3/4 in | 7/16 in

### Material Specifications

Material Type Hot dip galvanized steel

### Packaging and Weights

Packaging quantity 1

**Weight, net** 2 kg | 4.409 lb

# Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



# ACS-12



# CS-B



#### Cluster Support Bracket

#### **Product Classification**

Product Type Cluster Support Bracket

# General Specifications

Cable Runs, quantity 7
Hole, quantity 7

**Mounting** Cluster support

#### **Dimensions**

 Height
 127 mm | 5 in


 Width
 228.6 mm | 9 in

 Length
 152.4 mm | 6 in

 Pipe Outer Diameter
 60.96 mm | 2.4 in

 Hole Size
 3/4 in | 7/16 in

# Outline Drawing



# Material Specifications

Material Type Hot dip galvanized steel

# Packaging and Weights

**Included** Brackets

Packaging quantity 1

**Weight, net** 1.4 kg | 3.086 lb

# Regulatory Compliance/Certifications

Agency Classification



# CS-B

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



# GUB-4240



#### Galvanized U-bolt Assembly, 1/2 in x 2-1/2 in x 4 in

#### **Product Classification**

Product Type U-bolt

#### **Dimensions**

 Height
 101.6 mm | 4 in

 Width
 25.4 mm | 1 in

 Length
 101.6 mm | 4 in

 Pipe Outer Diameter
 12.7 mm | 0.5 in

 Throat Dimension
 63.5 mm | 2.5 in

#### Material Specifications

Material Type Hot dip galvanized steel

#### Packaging and Weights

Included Nuts | U-bolts | Washers

Packaging quantity 1

**Weight, net** 0.3 kg | 0.661 lb

# Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant







PIM-Guard® Antenna and RRU Cable Support Bracket with 8 ports for stackable hangers (up to 3 per port). Install with torque wrench set at 10 to 15 ft-lb to meet carrier PIM requirements. For patents, see www.cs-pat.com

#### **Product Classification**

Product Type Antenna/RRU Cable Support

Product Brand PIM-Guard®

#### General Specifications

Cable Runs, quantity 8
Hole, quantity 8

**Mounting** Pipe, 60.3–114.3 mm (2-3/8 in to 4-1/2 in) OD

#### **Dimensions**

 Height
 55.88 mm | 2.2 in

 Width
 248.92 mm | 9.8 in

 Length
 317.5 mm | 12.5 in

 Mounting Diameter, maximum
 60.96 mm | 2.4 in

 Mounting Diameter, minimum
 114.3 mm | 4.5 in

 Hole Size
 3/4 in | 7/16 in

### Material Specifications

Material Type Hot dip galvanized steel

### Packaging and Weights

Packaging quantity 1

**Weight, net** 4.1 kg | 9.039 lb

# Regulatory Compliance/Certifications

Agency Classification


CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant





PIM-Guard® Antenna and RRU Cable Support Bracket with 23 ports for stackable hangers (up to 3 per port). Install with torque wrench set at 10 to 15 ft-lb to meet carrier PIM requirements. For patents, see www.cs-pat. com

#### **Product Classification**

Product Type Antenna/RRU Cable Support

Product Brand PIM-Guard®

#### General Specifications

Cable Runs, quantity 23
Hole, quantity 23

**Mounting** Pipe, 60.3–114.3 mm (2-3/8 in to 4-1/2 in) OD

#### **Dimensions**

 Height
 55.88 mm | 2.2 in

 Width
 457.2 mm | 18 in

 Length
 419.1 mm | 16.5 in

 Mounting Diameter, maximum
 60.96 mm | 2.4 in

 Mounting Diameter, minimum
 114.3 mm | 4.5 in

 Hole Size
 3/4 in | 7/16 in

### Material Specifications

Material Type Hot dip galvanized steel

### Packaging and Weights

Packaging quantity 1

**Weight, net** 5.1 kg | 11.244 lb

# Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value


ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



# PG-CSEB17



PIM-Guard® Expansion Bracket - expands PG-CS08 Cable Support Bracket to 23 Ports. For patents, see www.cs-pat.com

#### **Product Classification**

Product Type Antenna/RRU Cable Support

Product Brand PIM-Guard®

#### General Specifications

Cable Runs, quantity 17
Hole, quantity 17

**Mounting** Pipe, 60.3–114.3 mm (2-3/8 in to 4-1/2 in) OD

#### **Dimensions**

 Height
 55.88 mm | 2.2 in

 Width
 457.2 mm | 18 in

 Length
 101.6 mm | 4 in

 Hole Size
 3/4 in | 7/16 in

# Material Specifications

Material Type Hot dip galvanized steel

### Packaging and Weights

Packaging quantity 1

**Weight, net** 0.8 kg | 1.764 lb

### Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant

# PG-CSEB17

UK-ROHS

Compliant



# PG-RM06



PIM-Guard® Round Member Cable Support Bracket 6 ports for stackable hangers (up to 3 per port). Install with torque wrench set at 5 to 7 ft-lb to meet carrier PIM requirements. For patents, see www.cs-pat.com

#### **Product Classification**

Product Type Antenna/RRU Cable Support

Product Brand PIM-Guard®

Ordering Note ANDREW® standard product (Global)

**Warranty** One year

### General Specifications

Cable Runs, quantity 6
Hole, quantity 6

**Mounting** Pipe, 60.3–88.9 mm (2-3/8 in to 3-1/2 in) OD

#### **Dimensions**

 Height
 50.8 mm | 2 in

 Width
 50.8 mm | 2 in

 Length
 198.12 mm | 7.8 in

 Mounting Diameter, maximum
 60.96 mm | 2.4 in

 Mounting Diameter, minimum
 88.9 mm | 3.5 in

Hole Size 3/4 in

#### Material Specifications

Material Type Hot dip galvanized steel

#### Packaging and Weights

Packaging quantity 1

**Weight, net** 2.3 kg | 5.071 lb

#### Regulatory Compliance/Certifications

Agency Classification

# PG-RM06

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



#### \* Footnotes

**Warranty** For more information, please consult our Product Warranty guidelines

# PG-RMBH12



PIM-Guard® Round Member Cable Support Bracket for Block Hangers - Two 3/8" threaded rods for up to 12 hangers. Install with torque wrench set at 10 to 15 ft-lb to meet carrier PIM requirements.

#### **Product Classification**

Product Type Antenna/RRU Cable Support

Product Brand PIM-Guard®

Ordering Note ANDREW® standard product (Global)

**Warranty** One year

### General Specifications

Cable Runs, quantity 12

**Mounting** Pipe, 60.3–88.9 mm (2-3/8 in to 3-1/2 in) OD

#### **Dimensions**

 Height
 38.1 mm | 1.5 in

 Width
 139.7 mm | 5.5 in

 Length
 304.8 mm | 12 in

 Mounting Diameter, maximum
 60.96 mm | 2.4 in

 Mounting Diameter, minimum
 88.9 mm | 3.5 in

### Material Specifications

Material Type Hot dip galvanized steel

### Packaging and Weights

Included Attachment hardware | Clamps | Threaded rod

Packaging quantity 1

**Weight, net** 2.6 kg | 5.732 lb

#### Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

# PG-RMBH12

# \* Footnotes

Warranty

For more information, please consult our Product Warranty guidelines



# PG-RMBH12-BP



PIM-Guard® Round Member Cable Support Bracket for Block Hangers (pkg of 10)- Two 3/8" threaded rods for up to 12 hangers. Install with torque wrench set at 10 to 15 ft-lb to meet carrier PIM requirements.

#### **Product Classification**

Product Type Antenna/RRU Cable Support

Product Brand PIM-Guard®

Ordering Note ANDREW® standard product (Global)

**Warranty** One year

### General Specifications

Cable Runs, quantity 12

**Mounting** Pipe, 60.3–88.9 mm (2-3/8 in to 3-1/2 in) OD

#### **Dimensions**

 Height
 38.1 mm | 1.5 in

 Width
 139.7 mm | 5.5 in

 Length
 304.8 mm | 12 in

 Mounting Diameter, maximum
 60.96 mm | 2.4 in

 Mounting Diameter, minimum
 88.9 mm | 3.5 in

### Material Specifications

Material Type Hot dip galvanized steel

### Packaging and Weights

Included Attachment hardware | Clamps | Threaded rod

Packaging quantity 10

**Weight, net** 2.6 kg | 5.732 lb

#### Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

# PG-RMBH12-BP

# \* Footnotes

Warranty

For more information, please consult our Product Warranty guidelines

