

CT-7812



Combination Tool (open end wrench for connector body, chamfer tool, file, inner conductor gauge, jacket cut-off gauge) for 1/2 in and 7/8 in coaxial cable

Product Classification

Product Type	Tool
Product Brand	HELIAX®
Ordering Note	CommScope® standard product in Europe, the Middle East, and Africa

General Specifications

Application	Prepares cable for connector attachment
Tool Type	Combination tool

Dimensions

Nominal Size	1/2 in 7/8 in
Wrench Opening	22.352 mm 0.88 in 35.052 mm 1.38 in

Material Specifications

Material Type	Steel
----------------------	-------

Mechanical Specifications

Torque Value	0 in lb 0 N-m
---------------------	-----------------

Packaging and Weights

Height, packed	66.04 mm 2.6 in
Length, packed	238.76 mm 9.4 in
Packaging quantity	1
Weight, gross	0.47 kg 1.036 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value

CT-7812

ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

