

CX8140-000 | RWGK-C-40/20

RWGK Heat-shrinkable wraparound kit for grounding cables with 20 to 40 mm cable diameter

- A lead-free method for grounding of double jacket cables
- Composite material provides high mechanical strength and ease of installation in confined spaces

OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

Regional Availability	EMEA
Product Type	Heat shrink grounding kit
Product Series	RWGK

General Specifications

Color	Black
Sealant Type	Hotmelt adhesive

Dimensions

Height	230 mm 9.055 in
Length	250 mm 9.843 in
Single Cable Diameter, maximum	40 mm 1.575 in
Single Cable Diameter, minimum	20 mm 0.787 in
Expanded Wall Thickness, minimum	1.5 mm 0.059 in

Material Specifications

Material Type	Fiber-reinforced multi-layer sealing sleeve
----------------------	---

Environmental Specifications

Environmental Space	Buried Ducted
----------------------------	-----------------

Packaging and Weights

Packaging quantity	1
Packaging Type	Bag Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

