

DHK-78-6-P



Double Hanger Kit for 7/8 in coaxial cable, triple stack; includes hardware and angle adapter

Product Classification

Product Type	Hanger kit
Product Brand	ValuSite™
Ordering Note	ANDREW® non-standard product

General Specifications

Cables per Hanger	6
Color	Black
Hanger Type	Composite clamp
Harmonized System (HS) Code	85366910 (Coaxial cable and other coaxial electric conductors)
Mounting	M8 hardware

Dimensions

Maximum Stack Height	3
Height	20.8 mm 0.819 in
Width	26.2 mm 1.031 in
Length	37.6 mm 1.48 in
Compatible Cable Diameter Range	27.7–28.2 mm
Compatible Diameter, maximum	28.2 mm 1.11 in
Compatible Diameter, minimum	27.5 mm 1.083 in
Nominal Size	7/8 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Engineered plastic Stainless steel 304
----------------------	--

DHK-78-6-P

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Corrosion Resistance, minimum with no degradation ≥500 hours in salt spray chamber

Environmental Strength Capability Double cable weight

UV Resistance, minimum with no degradation ≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed 20.3 cm | 7.992 in

Length, packed 15.2 cm | 5.984 in

Included Angle adapter | Hardware

Packaging quantity 1

Weight, gross 0.27 kg | 0.595 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power