

# ECI-10-292-4

---



HELIAX® 4" Boot Assembly for one 10 mm fiber cable and one or two 29 mm power cables

## Product Classification

<b>Product Type</b>	Boot assembly
<b>Product Brand</b>	HELIAX®
<b>Ordering Note</b>	CommScope® non-standard product

## General Specifications

<b>Cables per Cushion</b>	3
<b>Color</b>	Black

## Dimensions

<b>Height</b>	101.6 mm   4 in
<b>Width</b>	0 mm   0 in
<b>Length</b>	76.2 mm   3 in

## Material Specifications

<b>Material Type</b>	EPDM rubber
----------------------	-------------

## Environmental Specifications

<b>UV Resistance, minimum with no degradation</b>	≥1000 hours
---	-------------

## Packaging and Weights

<b>Height, packed</b>	170.18 mm   6.7 in
<b>Width, packed</b>	129.54 mm   5.1 in
<b>Length, packed</b>	99.06 mm   3.9 in
<b>Included</b>	Cushion

# ECI-10-292-4

---

**Packaging quantity** 1  
**Weight, gross** 0.9 kg | 1.984 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

