

# FA-3540-STH

---



Standard Butterfly Hanger and Grommet kit for HELIAX® Cables, 35-40mm

## Product Classification

**Product Type** Hanger kit

## General Specifications

**Cables per Hanger** 1  
**Color** Black | Silver  
**Hanger Type** Hanger kits  
**Mounting** 3/8 in (M10) drilled cable ladder

## Dimensions

**Height** 51.1 mm | 2.012 in  
**Compatible Diameter, maximum** 40 mm | 1.575 in  
**Compatible Diameter, minimum** 35 mm | 1.378 in  
**Nominal Size** 1-5/8 in

## Electrical Specifications

**Return Loss Effect, maximum** 0.1 dB  
**DTF Effect, maximum** 0.1 dB

## Material Specifications

**Material Type** EPDM rubber | Stainless steel

## Mechanical Specifications

**Vibration Survival** ≥4 hours at resonant frequency

## Environmental Specifications

# FA-3540-STH

---

<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
<b>Corrosion Resistance, minimum with no degradation</b>	≥500 hours in salt spray chamber
<b>Environmental Strength Capability</b>	Double cable weight

## Packaging and Weights

<b>Height, packed</b>	26 cm   10.236 in
<b>Width, packed</b>	9 cm   3.543 in
<b>Length, packed</b>	9 cm   3.543 in
<b>Packaging quantity</b>	10
<b>Weight, gross</b>	0.53 kg   1.168 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

