



FACT® MPO Module, left sided, LC at front side, 2x12 fiber MPO at rear side, Ultra Low Loss (ULL) multimode OM5, wiring method A straight

- Offers the same craft-friendly interface for LC and SC connectors as the cabled module
- Allow installers to connect an MPO trunk cable to turn up services in rapid installation applications

## Product Classification

Regional Availability	Asia   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber module
Product Brand	FACT®
Product Series	FACT

## General Specifications

Functionality	Breakout
Application	For Use with FACT NG4 Universal Chassis
Body Style	Left orientation
Color, boot	Black
Color, housing	Black
Color, rear	Lime green
Interface, front	LC/UPC
Interface Feature, front	Duplex
Interface Color, front	Lime green
Interface, rear	MPO
Interface Feature, rear	Key up/down   Male   Pinned
Interface Color, rear	Lime green
Polarity	Method A
Total Fibers, quantity	24
Total Ports, quantity, front	12
Total Ports, quantity, rear	2

## Dimensions

# 760251229 | FACT-MMDL5H-A

Height	13.21 mm   0.52 in
Width	159.77 mm   6.29 in
Depth	122.68 mm   4.83 in

## Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM5
Insertion Loss, maximum	0.4 dB
Insertion Loss, typical	0.32 dB
Return Loss, minimum	27 dB

## Environmental Specifications

Operating Temperature	-5 °C to +40 °C (+23 °F to +104 °F)
Storage Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 85%, non-condensing

## Packaging and Weights

Packaging quantity	1
Packaging Type	Bag   Carton

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

