L2SGRIP



Support Hoisting Grip with clamp for 0.4-0.56 in (10.2-14.2 mm) coaxial cable

Product Classification

Product Type Hoisting grip
Product Brand HELIAX®

Ordering Note ANDREW® non-standard product

General Specifications

Attachment Spacing Intervals60.96 m | 200 ftHoisting Grip TypeSupport hoisting gripInstallation ToolRequired, not included

Support Clamp Included

Tool Type Hoisting grip

Dimensions

Grip Length, minimum101.6 mm | 4 inLeader Length, minimum152.4 mm | 6 inCompatible Diameter, maximum14.2 mm | 0.559 inCompatible Diameter, minimum10.2 mm | 0.402 in

Nominal Size 3/8 in

Electrical Specifications

Return Loss Effect, maximum 0.1 dB **DTF Effect, maximum** 0.1 dB

Material Specifications

Material Type Stainless steel | Tin-coated bronze

Mechanical Specifications

Pull Load Capacity 158.757 kg | 350 lb



L2SGRIP

Packaging and Weights

 Height, packed
 25.4 mm | 1 in

 Width, packed
 177.8 mm | 7 in

 Length, packed
 127 mm | 5 in

Packaging quantity

Weight, gross 0.3 kg | 0.661 lb

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant