

L6SGRIP



Support Hoisting Grip for 1-1/4 in coaxial cable

Product Classification

Product Type	Hoisting grip
Ordering Note	CommScope® standard product (Global)

General Specifications

Attachment Spacing Intervals	60.96 m 200 ft
Hoisting Grip Type	Support hoisting grip
Installation Tool	Required, not included
Support Clamp	Included
Tool Type	Hoisting grip

Dimensions

Grip Length, minimum	609.6 mm 24 in
Leader Length, minimum	254 mm 10 in
Nominal Size	1-1/4 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Stainless steel
----------------------	-----------------

Mechanical Specifications

Pull Load Capacity	408.233 kg 900 lb
---------------------------	---------------------

Packaging and Weights

Packaging quantity	1
---------------------------	---

L6SGRIP

Weight, gross

0.38 kg | 0.838 lb

Regulatory Compliance/Certifications

Agency

Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system