

Double Click-on Hanger for 1-5/8 in coaxial cable - Hardware Sold Separately (search 243095-SERIES-HARDWARE for options available)

Product Classification

Product Type

Product Brand

Ordering Note

General Specifications

Cables per Hanger 1 Color Black Hanger Type Click-on hanger Mounting

Dimensions

Maximum Stack Height Height Width

Length **Compatible Cable Diameter Range Compatible Diameter, maximum Compatible Diameter, minimum** Nominal Size

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

HELIAX® ANDREW® non-standard product

Hanger kit

3/8 in (M10) drilled cable ladder

4
51.1 mm 2.012 in
79.5 mm 3.13 in
154.7 mm 6.091 in
49-51.1 mm
51.1 mm 2.012 in
49 mm 1.929 in
1-5/8 in

Page 1 of 2



L7CLICK

Material Type	Engineered plastic
Mechanical Specifications	
Vibration Survival	≥4 hours at resonant frequency
Environmental Specifications	
Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Environmental Strength Capability	Double cable weight
UV Resistance, minimum with no degradation	≥100 hours exposure in accelerated UV life chamber
Packaging and Weights	
Height, packed	12.9 cm 5.079 in
Width, packed	5.5 cm 2.165 in
Length, packed	5.9 cm 2.323 in
Packaging quantity	10
Weight, gross	1.6 kg 3.527 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power

Page 2 of 2



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 2, 2025