

# L7SGRIP

---



Support Hoisting Grip with clamp for 1.75-1.99 in (44.5-50.5 mm) coaxial cable

## Product Classification

<b>Product Type</b>	Hoisting grip
<b>Product Brand</b>	HELIAX®
<b>Ordering Note</b>	ANDREW® standard product in Europe, the Middle East, and Africa   ANDREW® standard product in Mexico, Central America, and South America   ANDREW® standard product in the United States and Canada

## General Specifications

<b>Attachment Spacing Intervals</b>	60.96 m   200 ft
<b>Hoisting Grip Type</b>	Support hoisting grip
<b>Installation Tool</b>	Required, not included
<b>Support Clamp</b>	Included
<b>Tool Type</b>	Hoisting grip

## Dimensions

<b>Grip Length, minimum</b>	685.8 mm   27 in
<b>Leader Length, minimum</b>	304.8 mm   12 in
<b>Compatible Diameter, maximum</b>	50.5 mm   1.988 in
<b>Compatible Diameter, minimum</b>	44.5 mm   1.752 in
<b>Nominal Size</b>	1-5/8 in

## Electrical Specifications

<b>Return Loss Effect, maximum</b>	0.1 dB
<b>DTF Effect, maximum</b>	0.1 dB

## Material Specifications

<b>Material Type</b>	Stainless steel
----------------------	-----------------

## Mechanical Specifications

# L7SGRIP

---

**Pull Load Capacity** 430.913 kg | 950 lb

## Packaging and Weights

**Packaging quantity** 1

**Weight, gross** 0.4 kg | 0.882 lb

## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015

### Classification

Designed, manufactured and/or distributed under this quality management system