

LUHG-38



Lace-up Hoisting Grip for HELIAX® 0.40-0.56 in (10.2-14.2 mm) cable including all RFFT discrete trunk series cables

Product Classification

Product Type	Hoisting grip
Product Brand	HELIAX®
Ordering Note	ANDREW® standard product (Global)

General Specifications

Attachment Spacing Intervals	60.96 m 200 ft
Hoisting Grip Type	Lace-up hoisting grip
Installation Tool	Required, not included
Support Clamp	Not included
Tool Type	Hoisting grip

Dimensions

Grip Length, minimum	152.4 mm 6 in
Leader Length, minimum	165.1 mm 6.5 in
Compatible Diameter, maximum	14.2 mm 0.559 in
Compatible Diameter, minimum	10.2 mm 0.402 in
Nominal Size	3/8 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Stainless steel
----------------------	-----------------

Mechanical Specifications

Pull Load Capacity	90.718 kg 200 lb
---------------------------	--------------------

LUHG-38

Packaging and Weights

Height, packed	55.88 mm 2.2 in
Width, packed	266.7 mm 10.5 in
Length, packed	266.7 mm 10.5 in
Packaging quantity	1
Weight, gross	0.04 kg 0.088 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

