

MS-100



Pipe-to-Pipe Adapter, adapts 1-1/2 in to 3-1/2 in OD pipe to 4 in to 9 in OD pipe

Product Classification

Product Type Adapter

General Specifications

Mounting Pipe-to-pipe

Tower Taper Non-tapered

Dimensions

Height	50.8 mm 2 in
Width	304.8 mm 12 in
Length	406.4 mm 16 in
Mounting Diameter 2, maximum	228.6 mm 9 in
Mounting Diameter 2, minimum	101.6 mm 4 in
Mounting Diameter, maximum	88.9 mm 3.5 in
Mounting Diameter, minimum	38.1 mm 1.5 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included	Clamp halves Threaded rod
Packaging quantity	2
Weight, net	11.3 kg 24.912 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system