# MT-373



Stainless Steel Threaded Rod, 3/8 in x 12 in

#### Product Classification

Product Type Threaded rod

#### Dimensions

| Height              | 25.4 mm   1 in    |
|---------------------|-------------------|
| Width               | 25.4 mm   1 in    |
| Length              | 304.8 mm   12 in  |
| Pipe Outer Diameter | 10.16 mm   0.4 in |
| Material Thickness  | 10.16 mm   0.4 in |

### Material Specifications

| Material Type | Stainless steel |
|---------------|-----------------|
|---------------|-----------------|

## Packaging and Weights

| Included           | Threaded rod      |
|--------------------|-------------------|
| Packaging quantity | 1                 |
| Weight, net        | 0.2 kg   0.441 lb |

### Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| CHINA-ROHS    | Below maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC    | Compliant as per SVHC revision on www.andrew.com/ProductCompliance             |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |



Page 1 of 1



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025