760251044 | EPX-2U-MOD-ENC



EPX 2U sliding panel, accepts (8) G2 style splice cassettes, modules or adapter packs, providing up to 96 duplex LC ports

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber patch panel | Fiber patch/splice panel

Product Series EPX

General Specifications

Application Accepts eight G2 modular cassettes

Color Black

Intelligence Type Not iPatch® ready

Interface, front Unloaded

Module/Adapter Pack Slots, quantity 8

Rack Type EIA 19 in

Rack Units 2

Shelf MovementSlidingTotal Fibers, quantity192Total Ports, quantity0

Dimensions

 Height
 88.9 mm | 3.5 in

 Width
 482.6 mm | 19 in

 Depth
 412.75 mm | 16.25 in

Environmental Specifications

Safety Standard CSA 22.2 | UL 1863

Packaging and Weights



760251044 | EPX-2U-MOD-ENC

1

Packaging quantity

Weight, net 4.481 kg | 9.88 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

