

760251098 | EPX-1U-MOD-OPEN-FX



EPX 1U open fixed panel, accepts (4) G2 style splice cassettes, modules or adapter packs, providing up to 48 duplex LC ports

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel
Product Series	EPX

General Specifications

Application	Accepts four G2 modular cassettes
Color	Black
Intelligence Type	Not iPatch® ready
Interface, front	Unloaded
Module/Adapter Pack Slots, quantity	4
Rack Type	EIA 19 in
Rack Units	1
Shelf Movement	Fixed
Total Fibers, quantity	96
Total Ports, quantity	0

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in
Depth	327.91 mm 12.91 in

Packaging and Weights

Packaging quantity	1
Weight, net	1.057 kg 2.33 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

